







## Placca Gira F200 bianco puro brillante



| Specifica   | Cod. ord. | UI   | EUR/pezzo IVA esclusa | SP | EAN           |
|---|-----------|------|-----------------------|----|---------------|
|  1 modulo                          | 0211 70   | 1/10 | 7,80                  | 01 | 4010337113171 |
|  2 moduli                        | 0212 70   | 1/10 | 13,77                 | 01 | 4010337113225 |
|  2 moduli senza costola centrale | 1002 70   | 1/10 | 13,77                 | 01 | 4010337113430 |
|  3 moduli                        | 0213 70   | 1/5  | 22,23                 | 01 | 4010337113270 |
|  4 moduli                        | 0214 70   | 1/5  | 35,78                 | 01 | 4010337113331 |
|  5 moduli                        | 0215 70   | 1/5  | 54,65                 | 01 | 4010337113386 |

### Caratteristiche

- Nella versione di colore bianco puro lucido: realizzato con l'85% di plastica bio-circolare.

### Dati tecnici

|                   |                           |
|-------------------|---------------------------|
| Placca 1-m:       | B 90,0 x H 90,0 x T 11,4  |
| Placca 2-m:       | B 90,0 x H 161,1 x T 11,4 |
| Placca 2-m s/COC: | B 90,0 x H 161,1 x T 11,4 |

|   |                           |
|---|---------------------------|
| Placca 3-m:   | B 90,0 x H 232,6 x T 11,4 |
| Placca 4-m:   | B 90,0 x H 303,9 x T 11,4 |
| Placca 5-m:   | B 90,0 x H 375,2 x T 11,4 |
| Raggio angolare:  | R 0,3                     |
| Plastica biocircolare<br>- Versione di colore: bianco puro brillante: | min. 50%                  |

---