







Placca Gira F300 bianco puro brillante



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 1 modulo	0211 80	1/10	7,77	01	4010337113478
 2 moduli	0212 80	1/10	10,67	01	4010337113539
 2 moduli senza costola centrale	1002 80	1/10	10,67	01	4010337131830
 3 moduli	0213 80	1/5	19,47	01	4010337113584
 4 moduli	0214 80	1/5	31,45	01	4010337113638
 5 moduli	0215 80	1/5	47,99	01	4010337131823

Caratteristiche

- Nella versione di colore bianco puro lucido: realizzato con l'85% di plastica bio-circolare.

Dati tecnici

Placca 1-m:	B 80,8 x H 80,8 x T 11,4
Placca 2-m:	B 80,8 x H 151,9 x T 11,4
Placca 2-m s/COC:	B 80,8 x H 151,9 x T 11,4

Placca 3-m:	B 80,8 x H 223,4 x T 11,4
Placca 4-m:	B 80,8 x H 297,7 x T 11,4
Placca 5-m:	B 80,8 x H 366,0 x T 11,4
Raggio angolare:	R 0,5
Plastica biocircolare - Versione di colore: bianco puro brillante:	min. 50%
