








Placca Gira Standard 55 bianco crema brillante



| Specifica | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN |
|---|-----------|----------|-----------------------|----|---------------|
|  1 modulo | 0211 01 | 1/10/100 | 3,21 | 21 | 4010337211013 |
|  1,5 moduli | 1001 01 | 1/10 | 4,33 | 01 | 4010337881247 |
|  2 moduli | 0212 01 | 1/10/100 | 5,48 | 21 | 4010337212010 |
|  2 moduli senza costola centrale | 1002 01 | 1/10 | 4,05 | 01 | 4010337002017 |
|  3 moduli | 0213 01 | 1/10/100 | 9,66 | 01 | 4010337213017 |
|  4 moduli | 0214 01 | 1/5 | 16,71 | 01 | 4010337214014 |
|  5 moduli | 0215 01 | 1/5 | 27,49 | 01 | 4010337215011 |

Caratteristiche

- Plastica: materiale termoplastico privo di alogeni, resistente agli urti e infrangibile

Avvisi

- Adatta anche per installazioni in canalina.
 - Placca (1 - 5 moduli) in combinazione con il set di guarnizioni adatta anche per l'installazione da incasso protetta dall'acqua secondo IP44.
-