

Placca Gira F100 bianco puro satinato (verniciato)



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 1 modulo	0211 172	1/10	12,60	11	4010337133506
 2 moduli	0212 172	1/10	19,13	11	4010337133513
 2 moduli senza costola centrale	1002 172	1/10	19,13	11	4010337133551
 3 moduli	0213 172	1/5	31,46	11	4010337133520
 4 moduli	0214 172	1/5	51,10	11	4010337133537
 5 moduli	0215 172	1/5	77,75	11	4010337133544

Dati tecnici

Placca 1-m:	B 83,3 x H 83,3 x T 10,6
Placca 2-m:	B 83,3 x H 154,4 x T 10,6
Placca 2-m s/COC:	B 83,3 x H 154,4 x T 10,6
Placca 3-m:	B 83,3 x H 225,9 x T 10,6
Placca 4-m:	B 83,3 x H 297,2 x T 10,6
Placca 5-m:	B 83,3 x H 368,5 x T 10,6
Raggio angolare:	R 3

