

## Placca Gira F100 bianco puro satinato (verniciato)



| Specifica                                                                                                           | Cod. ord. | UI   | EUR/pezzo IVA esclusa | SP | EAN           |
|---------------------------------------------------------------------------------------------------------------------|-----------|------|-----------------------|----|---------------|
|  1 modulo                          | 0211 172  | 1/10 | 12,60                 | 11 | 4010337133506 |
|  2 moduli                        | 0212 172  | 1/10 | 19,13                 | 11 | 4010337133513 |
|  2 moduli senza costola centrale | 1002 172  | 1/10 | 19,13                 | 11 | 4010337133551 |
|  3 moduli                        | 0213 172  | 1/5  | 31,46                 | 11 | 4010337133520 |
|  4 moduli                        | 0214 172  | 1/5  | 51,10                 | 11 | 4010337133537 |
|  5 moduli                        | 0215 172  | 1/5  | 77,75                 | 11 | 4010337133544 |

## Dati tecnici

|                   |                           |
|-------------------|---------------------------|
| Placca 1-m:       | B 83,3 x H 83,3 x T 10,6  |
| Placca 2-m:       | B 83,3 x H 154,4 x T 10,6 |
| Placca 2-m s/COC: | B 83,3 x H 154,4 x T 10,6 |
| Placca 3-m:       | B 83,3 x H 225,9 x T 10,6 |
| Placca 4-m:       | B 83,3 x H 297,2 x T 10,6 |
| Placca 5-m:       | B 83,3 x H 368,5 x T 10,6 |
| Raggio angolare:  | R 3                       |

