





## Placca Gira F200 per montaggio piatto antracite (verniciato)



| Specifica  | Cod. ord. | UI       | EUR/pezzo IVA esclusa | SP | EAN           |
|--|-----------|----------|-----------------------|----|---------------|
|  1 modulo   | 0211 735  | 1/10/100 | 12,63                 | 11 | 4010337108887 |
|  2 moduli | 0212 735  | 1/10     | 22,23                 | 11 | 4010337108962 |
|  3 moduli | 0213 735  | 1/5      | 34,22                 | 11 | 4010337109297 |
|  4 moduli | 0214 735  | 1/5      | 55,43                 | 11 | 4010337109341 |

### Caratteristiche

- Nella versione di colore bianco puro lucido: realizzato con l'85% di plastica bio-circolare.

### Dati tecnici

|  |                          |
|--|--------------------------|
| Placca 1-m:                                  | B 90,0 x H 90,0 x T 3,4  |
| Placca 2-m:                                  | B 90,0 x H 161,1 x T 3,4 |
| Placca 3-m:                                  | B 90,0 x H 232,6 x T 3,4 |
| Placca 4-m:                                  | B 90,0 x H 303,9 x T 3,4 |
| Raggio angolare:                             | R 0,3                    |
| Plastica biocircolare                        |                          |
| - Versione di colore: bianco puro brillante: | min. 50%                 |