

## Placca Gira F200 bianco puro satinato (verniciato)



| Specifica                                                                                                           | Cod. ord. | UI   | EUR/pezzo IVA esclusa | SP | EAN           |
|---------------------------------------------------------------------------------------------------------------------|-----------|------|-----------------------|----|---------------|
|  1 modulo                          | 0211 72   | 1/10 | 12,63                 | 11 | 4010337113188 |
|  2 moduli                        | 0212 72   | 1/10 | 22,23                 | 11 | 4010337113232 |
|  2 moduli senza costola centrale | 1002 72   | 1/10 | 22,23                 | 11 | 4010337113447 |
|  3 moduli                        | 0213 72   | 1/5  | 34,22                 | 11 | 4010337113287 |
|  4 moduli                        | 0214 72   | 1/5  | 55,43                 | 11 | 4010337113348 |
|  5 moduli                        | 0215 72   | 1/5  | 84,41                 | 11 | 4010337113393 |

## Dati tecnici

|                   |                           |
|-------------------|---------------------------|
| Placca 1-m:       | B 90,0 x H 90,0 x T 11,4  |
| Placca 2-m:       | B 90,0 x H 161,1 x T 11,4 |
| Placca 2-m s/COC: | B 90,0 x H 161,1 x T 11,4 |
| Placca 3-m:       | B 90,0 x H 232,6 x T 11,4 |
| Placca 4-m:       | B 90,0 x H 303,9 x T 11,4 |
| Placca 5-m:       | B 90,0 x H 375,2 x T 11,4 |
| Raggio angolare:  | R 0,3                     |

