







Placca Gira F300 antracite (verniciato)



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 1 modulo	0211 83	1/10	12,60	11	4010337113461
 2 moduli	0212 83	1/10	19,13	11	4010337113515
 2 moduli senza costola centrale	1002 83	1/10	19,13	11	4010337131878
 3 moduli	0213 83	1/5	31,46	11	4010337113560
 4 moduli	0214 83	1/5	51,10	11	4010337113614
 5 moduli	0215 83	1/5	77,75	11	4010337131861

Caratteristiche

- Nella versione di colore bianco puro lucido: realizzato con l'85% di plastica bio-circolare.

Dati tecnici

Placca 1-m:	B 80,8 x H 80,8 x T 11,4
Placca 2-m:	B 80,8 x H 151,9 x T 11,4
Placca 2-m s/COC:	B 80,8 x H 151,9 x T 11,4

Placca 3-m:	B 80,8 x H 223,4 x T 11,4
Placca 4-m:	B 80,8 x H 297,7 x T 11,4
Placca 5-m:	B 80,8 x H 366,0 x T 11,4
Raggio angolare:	R 0,5
Plastica biocircolare - Versione di colore: bianco puro brillante:	min. 50%
