







Placca Gira F300 grigio opaco (verniciato)



| Specifica | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN |
|---|-----------|------|-----------------------|----|---------------|
|  1 modulo | 0211 86 | 1/10 | 12,60 | 11 | 4010337113492 |
|  2 moduli | 0212 86 | 1/10 | 19,13 | 11 | 4010337113522 |
|  2 moduli senza costola centrale | 1002 86 | 1/10 | 19,13 | 11 | 4010337131915 |
|  3 moduli | 0213 86 | 1/5 | 31,46 | 11 | 4010337113577 |
|  4 moduli | 0214 86 | 1/5 | 51,10 | 11 | 4010337113621 |
|  5 moduli | 0215 86 | 1/5 | 77,75 | 11 | 4010337131908 |

Caratteristiche

- Nella versione di colore bianco puro lucido: realizzato con l'85% di plastica bio-circolare.

Dati tecnici

| | |
|-------------------|---------------------------|
| Placca 1-m: | B 80,8 x H 80,8 x T 11,4 |
| Placca 2-m: | B 80,8 x H 151,9 x T 11,4 |
| Placca 2-m s/COC: | B 80,8 x H 151,9 x T 11,4 |

| | |
|--|---------------------------|
| Placca 3-m: | B 80,8 x H 223,4 x T 11,4 |
| Placca 4-m: | B 80,8 x H 297,7 x T 11,4 |
| Placca 5-m: | B 80,8 x H 366,0 x T 11,4 |
| Raggio angolare: | R 0,5 |
| Plastica biocircolare | |
| - Versione di colore: bianco puro brillante: | min. 50% |
