









## Gammelt - Vecchio - Bilanciere



| Specifica   | Cod. ord. | UI       | EUR/pezzo IVA esclusa | SP | EAN           |
|---|-----------|----------|-----------------------|----|---------------|
|  bianco crema brillante  | 0296 01   | 1/10     | 4,32                  | 21 | 4010337296010 |
|  bianco puro brillante | 0296 03   | 1/10/100 | 4,32                  | 21 | 4010337296034 |
|  bianco puro satinato  | 0296 27   | 1/10/100 | 4,32                  | 21 | 4010337296270 |
|  antracite             | 0296 28   | 1/10/100 | 5,08                  | 11 | 4010337296287 |
|  color alluminio       | 0296 26   | 1/10     | 8,49                  | 11 | 4010337296263 |
|  nero opaco            | 0296 005  | 1/10     | 8,49                  | 11 | 4010337038061 |
|  grigio opaco          | 0296 015  | 1/10     | 8,49                  | 11 | 4010337080220 |
|  acciaio inox          | 0296 600  | 1/10     | 16,03                 | 11 | 4010337021667 |

## Avvisi

- Placca (1 - 5 moduli) dei programmi di interruttori Standard 55 e Gira E2, in combinazione con il set di guarnizioni, adatta anche per l'installazione di interruttori e pulsanti a bilanciere con protezione dall'acqua IP44 (non per il bilanciere a 2 moduli).
  - Soggetto a disponibilità.
-