









## Copertura con manopola per dimmer e potenziometro elettronico



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	0650 01	1/10/100	7,20	02	4010337650010
 bianco puro brillante	0650 03	1/10/100	7,20	02	4010337650034
 bianco puro satinato	0650 27	1/10	7,20	02	4010337650270
 antracite	0650 28	1/10	10,81	02	4010337650287
 color alluminio	0650 26	1/10	16,42	02	4010337650263
 nero opaco	0650 005	1/10	16,42	02	4010337036593
 grigio opaco	0650 015	1/10	16,42	02	4010337081210
 acciaio inox	0650 600	1	22,97	02	4010337022329