







Placca bianco puro brillante



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 1 modulo	0211 112	1/10	7,77	01	4010337043973
 2 moduli	0212 112	1/10	10,67	01	4010337044017
 2 moduli senza costola centrale	1002 112	1/10	10,67	01	4010337047094
 3 moduli	0213 112	1/5	19,47	01	4010337044031
 4 moduli	0214 112	1/5	31,45	01	4010337044055
 5 moduli	0215 112	1/5	47,99	01	4010337044079

Caratteristiche

- Infrangibile.
- Nella versione di colore bianco puro lucido: realizzato con l'85% di plastica bio-circolare.

Dati tecnici

Placca 1-m:	B 83,3 x H 83,3 x T 10,6
Placca 2-m:	B 83,3 x H 154,4 x T 10,6
Placca 2-m s/COC:	B 83,3 x H 154,4 x T 10,6

Placca 3-m:	B 83,3 x H 225,9 x T 10,6
Placca 4-m:	B 83,3 x H 297,2 x T 10,6
Placca 5-m:	B 83,3 x H 368,5 x T 10,6
Raggio angolare:	R 3
Plastica biocircolare	
- Versione di colore: bianco puro brillante:	min. 50%

Avvisi

- In combinazione con la flangia di guranizione, adatta anche per il montaggio da incasso IP44 (protezione dall'acqua).
