

## Placca Gira Esprit alluminio (anodizzato)



| Specifica                                                                                                           | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN           |
|---------------------------------------------------------------------------------------------------------------------|-----------|----|-----------------------|----|---------------|
|  1 modulo                          | 0211 17   | 1  | 47,54                 | 11 | 4010337211174 |
|  1,5 moduli                      | 1001 17   | 1  | 70,52                 | 11 | 4010337881513 |
|  2 moduli                        | 0212 17   | 1  | 81,31                 | 11 | 4010337212171 |
|  2 moduli senza costola centrale | 1002 17   | 1  | 81,31                 | 11 | 4010337002178 |
|  3 moduli                        | 0213 17   | 1  | 135,56                | 11 | 4010337213178 |
|  4 moduli                        | 0214 17   | 1  | 187,24                | 11 | 4010337214175 |

### Caratteristiche

- Alluminio anodizzato E 1 EV 1.