







Placca Gira F200 bianco puro satinato (verniciato)



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 1 modulo	0211 72	1/10	12,63	11	4010337113188
 2 moduli	0212 72	1/10	22,23	11	4010337113232
 2 moduli senza costola centrale	1002 72	1/10	22,23	11	4010337113447
 3 moduli	0213 72	1/5	34,22	11	4010337113287
 4 moduli	0214 72	1/5	55,43	11	4010337113348
 5 moduli	0215 72	1/5	84,41	11	4010337113393

Caratteristiche

- Nella versione di colore bianco puro lucido: realizzato con l'85% di plastica bio-circolare.

Dati tecnici

Placca 1-m:	B 90,0 x H 90,0 x T 11,4
Placca 2-m:	B 90,0 x H 161,1 x T 11,4
Placca 2-m s/COC:	B 90,0 x H 161,1 x T 11,4

Placca 3-m:	B 90,0 x H 232,6 x T 11,4
Placca 4-m:	B 90,0 x H 303,9 x T 11,4
Placca 5-m:	B 90,0 x H 375,2 x T 11,4
Raggio angolare:	R 0,3
Plastica biocircolare - Versione di colore: bianco puro brillante:	min. 50%
