










Altoparlante radio IP da incasso System 55



| Specifica | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN |
|---|-----------|----|-----------------------|----|---------------|
|  bianco crema brillante | 2282 01 | 1 | 28,44 | 03 | 4010337076230 |
|  bianco puro brillante | 2282 03 | 1 | 28,44 | 03 | 4010337076247 |
|  bianco puro satinato | 2282 27 | 1 | 28,44 | 03 | 4010337076254 |
|  antracite | 2282 28 | 1 | 30,62 | 03 | 4010337076261 |
|  color alluminio | 2282 26 | 1 | 33,36 | 03 | 4010337076162 |
|  nero opaco | 2282 005 | 1 | 33,36 | 03 | 4010337037286 |
|  grigio opaco | 2282 015 | 1 | 33,36 | 03 | 4010337083931 |
|  acciaio inox | 2282 600 | 1 | 38,28 | 03 | 4010337032861 |

Caratteristiche

- Altoparlante da collegare alla radio da incasso Gira.

Dati tecnici

| | |
|--|--------------------|
| Profondità di montaggio: | 32 mm |
| Sezione dei conduttori - Collegamento altoparlante/AUX: | 1,5mm ² |
| Impedenza: | 8 Ω |
| Temperatura ambiente: | da -5 °C a +50 °C |
