


## Altoparlante radio IP da incasso



| Specifica                                                                                                        | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN           |
|------------------------------------------------------------------------------------------------------------------|-----------|----|-----------------------|----|---------------|
|  bianco crema brillante         | 2282 01   | 1  | 28,44                 | 03 | 4010337076230 |
|  bianco puro brillante        | 2282 03   | 1  | 28,44                 | 03 | 4010337076247 |
|  bianco puro satinato         | 2282 27   | 1  | 28,44                 | 03 | 4010337076254 |
|  antracite                    | 2282 28   | 1  | 30,62                 | 03 | 4010337076261 |
|  color alluminio (verniciato) | 2282 26   | 1  | 33,36                 | 03 | 4010337076162 |
|  nero opaco (verniciato)      | 2282 005  | 1  | 33,36                 | 03 | 4010337037286 |
|  grigio opaco (verniciato)    | 2282 015  | 1  | 33,36                 | 03 | 4010337083931 |
|  acciaio inox                 | 2282 600  | 1  | 38,28                 | 03 | 4010337032861 |
|  aspetto in vetro nero        | 2282 05   | 1  | 38,28                 | 03 | 4010337889182 |

## Caratteristiche

- Altoparlante da collegare alla radio da incasso Gira.

---

## Dati tecnici

|                                                            |                    |
|------------------------------------------------------------|--------------------|
| Profondità di montaggio:                                   | 32 mm              |
| Sezione dei conduttori<br>- Collegamento altoparlante/AUX: | 1,5mm <sup>2</sup> |
| Impedenza:                                                 | 8 $\Omega$         |
| Temperatura ambiente:                                      | da -5 °C a +50 °C  |

---