









## Copertura con uscita inclinata a 30° e campo per targhetta per anello di supporto jack modulare 2 canali



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	2640 01	1/10	8,89	01	4010337460114
 bianco puro brillante	2640 03	1/10	8,89	01	4010337460138
 bianco puro satinato	2640 27	1/10	8,89	01	4010337460183
 antracite	2640 28	1/10	11,73	11	4010337460190
 color alluminio	2640 26	1/10	16,02	11	4010337460176
 nero opaco	2640 005	1/10	16,02	11	4010337036500
 grigio opaco	2640 015	1/10	16,02	11	4010337085195
 acciaio inox	2640 600	1/10	20,17	11	4010337021582

## Contenuto della fornitura

- Targhetta con scritta in bianco in dotazione.
-