








**Presse doppia SCHUKO 16 A 250 V~ con maggiore protezione contro i contatti accidentali (Safety Plus) per scatola da incasso 1 modulo**



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	2731 01	1/10	22,32	01	4010337881100
 bianco puro brillante	2731 03	1/10	22,32	01	4010337881117
 bianco puro satinato	2731 27	1/10	22,32	01	4010337881124
 antracite	2731 28	1/10	25,02	11	4010337000778
 color alluminio	2731 26	1/10	29,17	11	4010337000761
 nero opaco	2731 005	1/10	29,17	11	4010337037538
 grigio opaco	2731 015	1/10	29,17	11	4010337085256

## Dati tecnici

Profondità di montaggio:	25 mm
Sezione dei conduttori - per conduttori da:	da 1,5 mm <sup>2</sup> a 2,5 mm <sup>2</sup>
Temperatura ambiente - maggiore protezione contro i contatti accidentali:	da 0 °C a +45 °C

Altezza di montaggio: 17,5 mm

---

## Avvisi

- Adatta per ogni normale scatola di installazione disponibile in commercio.
  - Maggiore protezione contro i contatti accidentali (Safety Plus) ai sensi della norma DIN VDE 0620-1.
-