








Interruttore di controllo a bilanciere British Standard (BS EN 60669-1) 20 AX 250 V~con bilanciere Interruttore a 2 poli



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	2834 01	1/10	46,92	29	4010337078814
 bianco puro brillante	2834 03	1/10	46,92	29	4010337078821
 antracite	2834 28	1/10	47,43	29	4010337078845
 color alluminio	2834 26	1/10	50,54	29	4010337078838
 nero opaco	2834 005	1/10	50,54	29	4010337038573
 grigio opaco	2834 015	1/10	50,54	29	4010337087137
 acciaio inox	2834 600	1/10	57,72	29	4010337022305

Dati tecnici

Profondità di montaggio:	24 mm
Sezione dei conduttori - per conduttori fino a:	2 x 4 mm ² o 1 x 6 mm ²

Avvisi

- Solo per fissaggio a viti.
 - BS EN 60669-1.
-