






Interruttore a bilanciere British Standard (BS EN 60669-1) 20 AX 250 V~ con bilanciere Interruttore a 2 poli



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	2836 01	1/10	38,99	29	4010337078944
 bianco puro brillante	2836 03	1/10	38,99	29	4010337078951
 antracite	2836 28	1/10	39,71	29	4010337078975
 color alluminio	2836 26	1/10	42,87	29	4010337078968
 nero opaco	2836 005	1/10	42,87	29	4010337038566
 grigio opaco	2836 015	1/10	42,87	29	4010337087144
 acciaio inox	2836 600	1/10	49,81	29	4010337021933

Dati tecnici

Profondità di montaggio:	24 mm
Sezione dei conduttori - per conduttori fino a:	2 x 4 mm ² o 1 x 6 mm ²

Avvisi

- Solo per fissaggio a viti.
 - BS EN 60669-1.
-