

## Pulsante a bilanciere 3 moduli 10 A 250 V~ con bilanciere Contatto di chiusura a 1 polo



| Specifica                                                                                                     | Cod. ord. | UI   | EUR/pezzo IVA esclusa | SP | EAN           |
|---------------------------------------------------------------------------------------------------------------|-----------|------|-----------------------|----|---------------|
|  bianco crema brillante      | 2844 01   | 1/10 | 38,42                 | 29 | 4010337082033 |
|  bianco puro brillante     | 2844 03   | 1/10 | 38,42                 | 29 | 4010337082040 |
|  antracite                 | 2844 28   | 1/10 | 41,20                 | 29 | 4010337082064 |
|  color alluminio           | 2844 26   | 1/10 | 45,30                 | 29 | 4010337082057 |
|  nero opaco                | 2844 005  | 1/10 | 45,30                 | 29 | 4010337037903 |
|  grigio opaco              | 2844 015  | 1/10 | 45,30                 | 29 | 4010337087182 |
|  acciaio inox (verniciato) | 2844 600  | 1/10 | 49,19                 | 29 | 4010337021957 |

### Dati tecnici

Profondità di montaggio: 25 mm

Sezione dei conduttori  
- per conduttori fino a: 2,5mm<sup>2</sup>

## Avvisi

- Solo per fissaggio a viti.

---