









Bilanciere 2 moduli non stampato System 55



| Specifica | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN |
|---|-----------|-----|-----------------------|----|---------------|
|  bianco crema brillante | 5370 01 | 1/5 | 8,35 | 02 | 4010337108498 |
|  bianco puro brillante | 5370 03 | 1/5 | 8,35 | 02 | 4010337108511 |
|  bianco puro satinato | 5370 27 | 1/5 | 8,35 | 02 | 4010337108535 |
|  antracite | 5370 28 | 1/5 | 11,43 | 02 | 4010337108542 |
|  color alluminio | 5370 26 | 1/5 | 13,48 | 02 | 4010337108528 |
|  nero opaco | 5370 005 | 1/5 | 13,48 | 02 | 4010337108474 |
|  grigio opaco | 5370 015 | 1/5 | 13,48 | 02 | 4010337108481 |
|  acciaio inox | 5370 600 | 1/5 | 17,34 | 02 | 4010337108559 |

Caratteristiche

- Bilancieri di comando senza stampa come ricambio per i bilancieri originali contrassegnati con simboli.
 - Utilizzabili in modo universale per il bilanciere sinistro e destro.
-

Avvisi

- Se si utilizza un pannello di metallo e/o una placca di metallo, la portata può diminuire.
-