










Bilanciere 1 modulo non stampato con finestra di controllo System 55



| Specifica | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN |
|---|-----------|-----|-----------------------|----|---------------|
|  • bianco crema brillante | 5371 01 | 1/5 | 6,41 | 02 | 4010337108337 |
|  • bianco puro brillante | 5371 03 | 1/5 | 6,41 | 02 | 4010337108344 |
|  • bianco puro satinato | 5371 27 | 1/5 | 6,41 | 02 | 4010337108351 |
|  • antracite | 5371 28 | 1/5 | 9,64 | 02 | 4010337108368 |
|  • color alluminio | 5371 26 | 1/5 | 11,56 | 02 | 4010337108375 |
|  • nero opaco | 5371 005 | 1/5 | 11,56 | 02 | 4010337108382 |
|  • grigio opaco | 5371 015 | 1/5 | 11,56 | 02 | 4010337108399 |
|  • acciaio inox | 5371 600 | 1/5 | 17,34 | 02 | 4010337108405 |

Caratteristiche

- Bilanciere di comando senza stampa come sostituzione del bilanciere originale contrassegnato con simboli.

Avvisi

- Se si utilizza un pannello di metallo e/o una placca di metallo, la portata può diminuire.
