


## Modulo calotta dati per jack modulare AMP



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 2 moduli	0039 00	1/5/25	6,35	01	4010337039006

### Avvisi

- Adatto per:AMP a 6 poli 1116603--1 toolless cat.3AMP 8 poli 1116515-1 cat.5e schermatoAMP 8 poli 1116604-1 toolless cat.5e non schermatoAMP 8 poli 1339015-1 toolless cat.5e schermatoAMP 8 poli 1375055-1 SL cat.6 non schermatoAMP 8 poli 1375188-1 SL cat.6 schermatosnap in jack RJ45Kannegieter BICC Brand RexKrone Inline RJ45 schermato/non schermatoAMP SL serie RJ45 jack cat.5EAMP TWIST-7AS SL jack 8 poli 1711441-1 schermato cat.7AMP TWIST-7AS SL jack 8 poli 1711437-1 schermato cat.7AMP TWIST-6S SL jack 8 poli 1711160-1 schermato cat.6AMP TWIST-6S SL jack 8 poli 1711342-1 schermato cat.6AMP TWIST-6AS SL jack 8 poli 1711592-1 schermato cat.6AMP TWIST-6AS SL jack 8 poli 1711716-1 schermato cat.6AMP LC LWL adattatore duplexAMP MT RJ LWL duplex.
- Seconda apertura chiudibile.