







## Placca Gira F100 antracite (verniciato)



| Specifica   | Cod. ord. | UI   | EUR/pezzo IVA esclusa | SP | EAN           |
|---|-----------|------|-----------------------|----|---------------|
|  1 modulo                          | 0211 173  | 1/10 | 12,60                 | 11 | 4010337135951 |
|  2 moduli                        | 0212 173  | 1/10 | 19,13                 | 11 | 4010337133568 |
|  2 moduli senza costola centrale | 1002 173  | 1/10 | 19,13                 | 11 | 4010337133605 |
|  3 moduli                        | 0213 173  | 1/5  | 31,46                 | 11 | 4010337133575 |
|  4 moduli                        | 0214 173  | 1/5  | 51,10                 | 11 | 4010337133582 |
|  5 moduli                        | 0215 173  | 1/5  | 77,75                 | 11 | 4010337133599 |

### Caratteristiche

- Nella versione di colore bianco puro lucido: realizzato con l'85% di plastica bio-circolare.

### Dati tecnici

|                   |                           |
|-------------------|---------------------------|
| Placca 1-m:       | B 83,3 x H 83,3 x T 10,6  |
| Placca 2-m:       | B 83,3 x H 154,4 x T 10,6 |
| Placca 2-m s/COC: | B 83,3 x H 154,4 x T 10,6 |

Placca 3-m: B 83,3 x H 225,9 x T 10,6

Placca 4-m: B 83,3 x H 297,2 x T 10,6

Placca 5-m: B 83,3 x H 368,5 x T 10,6

Raggio angolare: R 3

Plastica biocircolare

- Versione di colore: bianco puro brillante: min. 50%

---