







## Placca Gira F200 grigio opaco (verniciato)



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 1 modulo	0211 76	1/10	12,63	11	4010337113164
 2 moduli	0212 76	1/10	22,23	11	4010337113218
 2 moduli senza costola centrale	1002 76	1/10	22,23	11	4010337113423
 3 moduli	0213 76	1/5	34,22	11	4010337113263
 4 moduli	0214 76	1/5	55,43	11	4010337113324
 5 moduli	0215 76	1/5	84,41	11	4010337113379

### Caratteristiche

- Nella versione di colore bianco puro lucido: realizzato con l'85% di plastica bio-circolare.

### Dati tecnici

Placca 1-m:	B 90,0 x H 90,0 x T 11,4
Placca 2-m:	B 90,0 x H 161,1 x T 11,4
Placca 2-m s/COC:	B 90,0 x H 161,1 x T 11,4

Placca 3-m: B 90,0 x H 232,6 x T 11,4

Placca 4-m: B 90,0 x H 303,9 x T 11,4

Placca 5-m: B 90,0 x H 375,2 x T 11,4

Raggio angolare: R 0,3

Plastica biocircolare

- Versione di colore: bianco puro brillante: min. 50%

---