







## Placca Gira F200 bianco puro brillante



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 1 modulo	0211 70	1/10	7,80	01	4010337113171
 2 moduli	0212 70	1/10	13,77	01	4010337113225
 2 moduli senza costola centrale	1002 70	1/10	13,77	01	4010337113430
 3 moduli	0213 70	1/5	22,23	01	4010337113270
 4 moduli	0214 70	1/5	35,78	01	4010337113331
 5 moduli	0215 70	1/5	54,65	01	4010337113386

### Dati tecnici

Placca 1-m:	B 90,0 x H 90,0 x T 11,4
Placca 2-m:	B 90,0 x H 161,1 x T 11,4
Placca 2-m s/COC:	B 90,0 x H 161,1 x T 11,4
Placca 3-m:	B 90,0 x H 232,6 x T 11,4
Placca 4-m:	B 90,0 x H 303,9 x T 11,4
Placca 5-m:	B 90,0 x H 375,2 x T 11,4
Raggio angolare:	R 0,3

Plastica biocircolare

- Versione di colore: bianco puro brillante: min. 50%

---