









Copertura con manopola per dimmer e potenziometro elettronico



| Specifica | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN |
|---|-----------|----------|-----------------------|----|---------------|
|  bianco crema brillante | 0650 01 | 1/10/100 | 7,20 | 02 | 4010337650010 |
|  bianco puro brillante | 0650 03 | 1/10/100 | 7,20 | 02 | 4010337650034 |
|  bianco puro satinato | 0650 27 | 1/10 | 7,20 | 02 | 4010337650270 |
|  antracite | 0650 28 | 1/10 | 10,81 | 02 | 4010337650287 |
|  color alluminio | 0650 26 | 1/10 | 16,42 | 02 | 4010337650263 |
|  nero opaco | 0650 005 | 1/10 | 16,42 | 02 | 4010337036593 |
|  grigio opaco | 0650 015 | 1/10 | 16,42 | 02 | 4010337081210 |
|  acciaio inox | 0650 600 | 1 | 22,97 | 02 | 4010337022329 |