

## Copertura con manopola per dimmer e potenziometro elettronico



| Specifica                                                                                                        | Cod. ord. | UI       | EUR/pezzo IVA esclusa | SP | EAN           |
|------------------------------------------------------------------------------------------------------------------|-----------|----------|-----------------------|----|---------------|
|  bianco crema brillante         | 0650 01   | 1/10/100 | 7,20                  | 02 | 4010337650010 |
|  bianco puro brillante        | 0650 03   | 1/10/100 | 7,20                  | 02 | 4010337650034 |
|  bianco puro satinato         | 0650 27   | 1/10     | 7,20                  | 02 | 4010337650270 |
|  antracite                    | 0650 28   | 1/10     | 10,81                 | 02 | 4010337650287 |
|  color alluminio (verniciato) | 0650 26   | 1/10     | 16,42                 | 02 | 4010337650263 |
|  nero opaco (verniciato)      | 0650 005  | 1/10     | 16,42                 | 02 | 4010337036593 |
|  grigio opaco (verniciato)    | 0650 015  | 1/10     | 16,42                 | 02 | 4010337081210 |
|  acciaio inox                 | 0650 600  | 1        | 22,97                 | 02 | 4010337022329 |