








Placca Gira E2 bianco puro satinato



| Specifica | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN |
|---|-----------|----------|-----------------------|----|---------------|
|  1 modulo | 0211 22 | 1/10/100 | 7,77 | 01 | 4010337211228 |
|  1,5 moduli | 1001 22 | 1/10 | 11,50 | 01 | 4010337881322 |
|  2 moduli | 0212 22 | 1/10/100 | 10,67 | 01 | 4010337212225 |
|  2 moduli senza costola centrale | 1002 22 | 1/10 | 10,67 | 01 | 4010337002222 |
|  3 moduli | 0213 22 | 1/5 | 19,47 | 01 | 4010337213222 |
|  4 moduli | 0214 22 | 1/5 | 31,45 | 01 | 4010337214229 |
|  5 moduli | 0215 22 | 1/5 | 47,99 | 01 | 4010337215226 |

Caratteristiche

- Plastica: materiale termoplastico privo di alogeni, resistente agli urti e infrangibile

Avvisi

- Adatta anche per installazioni in canalina.
 - Placca (1 - 5 moduli) in combinazione con il set di guarnizioni adatta anche per l'installazione da incasso protetta dall'acqua secondo IP44.
-