

## Placca Gira Standard 55 bianco puro satinato



| Specifica                                                                                                           | Cod. ord. | UI       | EUR/pezzo IVA esclusa | SP | EAN           |
|---------------------------------------------------------------------------------------------------------------------|-----------|----------|-----------------------|----|---------------|
|  1 modulo                          | 0211 04   | 1/10/100 | 3,21                  | 21 | 4010337211044 |
|  1,5 moduli                      | 1001 04   | 1/10     | 4,33                  | 01 | 4010337881315 |
|  2 moduli                        | 0212 04   | 1/10/100 | 5,48                  | 21 | 4010337212041 |
|  2 moduli senza costola centrale | 1002 04   | 1/10     | 4,05                  | 01 | 4010337002048 |
|  3 moduli                        | 0213 04   | 1/10/100 | 9,66                  | 01 | 4010337213048 |
|  4 moduli                        | 0214 04   | 1/5      | 16,71                 | 01 | 4010337214045 |
|  5 moduli                        | 0215 04   | 1/5      | 27,49                 | 01 | 4010337215042 |

### Caratteristiche

- Plastica: materiale termoplastico privo di alogeni, resistente agli urti e infrangibile

## Avvisi

- Adatta anche per installazioni in canalina.
  - Placca (1 - 5 moduli) in combinazione con il set di guarnizioni adatta anche per l'installazione da incasso protetta dall'acqua secondo IP44.
-