








Presse doppia SCHUKO 16 A 250 V~ con maggiore protezione contro i contatti accidentali (Safety Plus) per scatola da incasso 1,5 moduli



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	2735 01	1/10	22,32	01	4010337000822
 bianco puro brillante	2735 03	1/10	22,32	01	4010337771371
 bianco puro satinato	2735 27	1/10	22,32	01	4010337771555
 antracite	2735 28	1/10	25,02	11	4010337771364
 color alluminio	2735 26	1/10	29,17	11	4010337000785
 nero opaco	2735 005	1/10	29,17	11	4010337037521
 grigio opaco	2735 015	1/10	29,17	11	4010337085294

Dati tecnici

Profondità di montaggio:	25 mm
Sezione dei conduttori - per conduttori da:	da 1,5 mm ² a 2,5 mm ²
Altezza di montaggio:	6 mm

Avvisi

- Adatta per scatole di installazione compatte Attema UK 40 e tipo H 140 di ABB/HAF.
 - Maggiore protezione contro i contatti accidentali (Safety Plus) ai sensi della norma DIN VDE 0620-1.
-