

Pulsante a bilanciere 3 moduli 10 A 250 V~ con bilanciere Contatto di chiusura a 1 polo



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 bianco crema brillante	2844 01	1/10	38,42	29	4010337082033
 bianco puro brillante	2844 03	1/10	38,42	29	4010337082040
 antracite	2844 28	1/10	41,20	29	4010337082064
 color alluminio	2844 26	1/10	45,30	29	4010337082057
 nero opaco	2844 005	1/10	45,30	29	4010337037903
 grigio opaco	2844 015	1/10	45,30	29	4010337087182
 acciaio inox (verniciato)	2844 600	1/10	49,19	29	4010337021957

Dati tecnici

Profondità di montaggio: 25 mm

Sezione dei conduttori
- per conduttori fino a: 2,5mm²

Avvisi

- Solo per fissaggio a viti.
