










## Bilanciere 1 modulo non stampato con finestra di controllo System 55



Specifica	Cod. ord.	UI	EUR/pezzo IVA esclusa	SP	EAN
 • bianco crema brillante	5371 01	1/5	6,41	02	4010337108337
 • bianco puro brillante	5371 03	1/5	6,41	02	4010337108344
 • bianco puro satinato	5371 27	1/5	6,41	02	4010337108351
 • antracite	5371 28	1/5	9,64	02	4010337108368
 • color alluminio	5371 26	1/5	11,56	02	4010337108375
 • nero opaco	5371 005	1/5	11,56	02	4010337108382
 • grigio opaco	5371 015	1/5	11,56	02	4010337108399
 • acciaio inox	5371 600	1/5	17,34	02	4010337108405

## Caratteristiche

- Bilanciere di comando senza stampa come sostituzione del bilanciere originale contrassegnato con simboli.

---

## Avvisi

- Se si utilizza un pannello di metallo e/o una placca di metallo, la portata può diminuire.

---