








## Pulsante scrivibile System 106



| Specifica  | Cod. ord. | UI | EUR/pezzo IVA esclusa | SP | EAN           |
|--|-----------|----|-----------------------|----|---------------|
|  acciaio inox                   | 5549 920  | 1  | 51,00                 | 20 | 4010337022800 |
|  alluminio                    | 5549 926  | -  | -                     | -  | 4010337022794 |
|  bianco traffico (verniciato) | 5549 902  | 1  | 39,22                 | 20 | 4010337022787 |
|  acciaio inox V4A             | 5549 914  | 1  | 69,08                 | 20 | 4010337092056 |
|  bronzo                       | 5549 921  | 1  | 69,08                 | 20 | 4010337100928 |
|  nero opaco (verniciato)      | 5549 925  | 1  | 69,08                 | 20 | 4010337100768 |

### Dati tecnici

Dimensioni

- H x L:

25,3 x 105,5

### Avvisi

- Questo prodotto può essere ordinato esclusivamente tramite il servizio per targhette Gira.
  - Scritte professionali mediante il servizio per targhette Gira [www.beschriftung.gira.de](http://www.beschriftung.gira.de).
- 

## **Contenuto della fornitura**

- Incl. dicitura stampata a laser personalizzata.
-