










Lautsprecher Unterputz-Radio IP System 55



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Cremeweiß glänzend	2282 01	1	28,44	03	4010337076230
 Reinweiß glänzend	2282 03	1	28,44	03	4010337076247
 Reinweiß seidenmatt	2282 27	1	28,44	03	4010337076254
 Anthrazit	2282 28	1	30,62	03	4010337076261
 Farbe Alu	2282 26	1	33,36	03	4010337076162
 Schwarz matt	2282 005	1	33,36	03	4010337037286
 Grau matt	2282 015	1	33,36	03	4010337083931
 Edelstahl	2282 600	1	38,28	03	4010337032861

Merkmale

- Lautsprecher zum Anschluss an das Gira Unterputz-Radio.

Technische Daten

Einbautiefe:	32 mm
Anschlussquerschnitt - Lautsprecher-/AUX-Anschluss:	1,5 mm ²
Impedanz:	8 Ω
Umgebungstemperatur:	-5 °C bis +50 °C
