







Afdekraam Gira F100 antraciet (gelakt)



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 1-voudig	0211 173	1/10	12,60	11	4010337135951
 2-voudig	0212 173	1/10	19,13	11	4010337133568
 2-voudig zonder middenstijl	1002 173	1/10	19,13	11	4010337133605
 3-voudig	0213 173	1/5	31,46	11	4010337133575
 4-voudig	0214 173	1/5	51,10	11	4010337133582
 5-voudig	0215 173	1/5	77,75	11	4010337133599

Merkmale

- In de kleurvariant puur wit glanzend: bestaat voor 85 % uit bio-circulair kunststof.

Technische Daten

Afdekraam 1-v:	B 83,3 x H 83,3 x T 10,6
Afdekkraam 2-v:	B 83,3 x H 154,4 x T 10,6
Afdekraam 2-v z/ms:	B 83,3 x H 154,4 x T 10,6

Afdekraam 3-v: B 83,3 x H 225,9 x T 10,6

Afdekraam 4-v: B 83,3 x H 297,2 x T 10,6

Afdekraam 5f: B 83,3 x H 368,5 x T 10,6

Hoekradius: R 3

Biocirculair kunststof

- Kleurvariant: zuiver wit glanzend: min. 50%
