







## Afdekraam Gira F200 antraciet (gelakt)



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 1-voudig	0211 73	1/10	12,63	11	4010337113157
 2-voudig	0212 73	1/10	22,23	11	4010337113201
 2-voudig zonder middenstijl	1002 73	1/10	22,23	11	4010337113416
 3-voudig	0213 73	1/5	34,22	11	4010337113256
 4-voudig	0214 73	1/5	55,43	11	4010337113317
 5-voudig	0215 73	1/5	84,41	11	4010337113362

### Merkmale

- In de kleurvariant puur wit glanzend: bestaat voor 85 % uit bio-circulair kunststof.

### Technische Daten

Afdekraam 1-v:	B 90,0 x H 90,0 x T 11,4
Afdekkraam 2-v:	B 90,0 x H 161,1 x T 11,4
Afdekraam 2-v z/ms:	B 90,0 x H 161,1 x T 11,4

Afdekraam 3-v:	B 90,0 x H 232,6 x T 11,4
Afdekraam 4-v:	B 90,0 x H 303,9 x T 11,4
Afdekraam 5f:	B 90,0 x H 375,2 x T 11,4
Hoekradius:	R 0,3
Biocirculair kunststof	
- Kleurvariant: zuiver wit glanzend:	min. 50%

---