







Afdekraam Gira F300 antraciet (gelakt)



| Spezifikation | Bestell-Nr. | VE | EUR/Stück o. MWSt. | PS | EAN |
|---|-------------|------|--------------------|----|---------------|
|  1-voudig | 0211 83 | 1/10 | 12,60 | 11 | 4010337113461 |
|  2-voudig | 0212 83 | 1/10 | 19,13 | 11 | 4010337113515 |
|  2-voudig zonder middenstijl | 1002 83 | 1/10 | 19,13 | 11 | 4010337131878 |
|  3-voudig | 0213 83 | 1/5 | 31,46 | 11 | 4010337113560 |
|  4-voudig | 0214 83 | 1/5 | 51,10 | 11 | 4010337113614 |
|  5-voudig | 0215 83 | 1/5 | 77,75 | 11 | 4010337131861 |

Merkmale

- In de kleurvariant puur wit glanzend: bestaat voor 85 % uit bio-circulair kunststof.

Technische Daten

| | |
|---------------------|---------------------------|
| Afdekraam 1-v: | B 80,8 x H 80,8 x T 11,4 |
| Afdekkraam 2-v: | B 80,8 x H 151,9 x T 11,4 |
| Afdekraam 2-v z/ms: | B 80,8 x H 151,9 x T 11,4 |

| | |
|--------------------------------------|---------------------------|
| Afdekraam 3-v: | B 80,8 x H 223,4 x T 11,4 |
| Afdekraam 4-v: | B 80,8 x H 297,7 x T 11,4 |
| Afdekraam 5f: | B 80,8 x H 366,0 x T 11,4 |
| Hoekradius: | R 0,5 |
| Biocirculair kunststof | |
| - Kleurvariant: zuiver wit glanzend: | min. 50% |
