







## Afdekraam Gira F100 antraciet (gelakt)



| Spezifikation   | Bestell-Nr. | VE   | EUR/Stück o. MWSt. | PS | EAN           |
|---|-------------|------|--------------------|----|---------------|
|  1-voudig                      | 0211 173    | 1/10 | 12,60              | 11 | 4010337135951 |
|  2-voudig                    | 0212 173    | 1/10 | 19,13              | 11 | 4010337133568 |
|  2-voudig zonder middenstijl | 1002 173    | 1/10 | 19,13              | 11 | 4010337133605 |
|  3-voudig                    | 0213 173    | 1/5  | 31,46              | 11 | 4010337133575 |
|  4-voudig                    | 0214 173    | 1/5  | 51,10              | 11 | 4010337133582 |
|  5-voudig                    | 0215 173    | 1/5  | 77,75              | 11 | 4010337133599 |

### Merkmale

- In de kleurvariant puur wit glanzend: bestaat voor 85 % uit bio-circulair kunststof.

### Technische Daten

|                     |                           |
|---------------------|---------------------------|
| Afdekraam 1-v:      | B 83,3 x H 83,3 x T 10,6  |
| Afdekkraam 2-v:     | B 83,3 x H 154,4 x T 10,6 |
| Afdekraam 2-v z/ms: | B 83,3 x H 154,4 x T 10,6 |

Afdekraam 3-v: B 83,3 x H 225,9 x T 10,6

Afdekraam 4-v: B 83,3 x H 297,2 x T 10,6

Afdekraam 5f: B 83,3 x H 368,5 x T 10,6

Hoekradius: R 3

Biocirculair kunststof  
- Kleurvariant: zuiver wit glanzend: min. 50%

---