







## Afdekraam Gira F200 antraciet (gelakt)



| Spezifikation   | Bestell-Nr. | VE   | EUR/Stück o. MWSt. | PS | EAN           |
|---|-------------|------|--------------------|----|---------------|
|  1-voudig                      | 0211 73     | 1/10 | 12,63              | 11 | 4010337113157 |
|  2-voudig                    | 0212 73     | 1/10 | 22,23              | 11 | 4010337113201 |
|  2-voudig zonder middenstijl | 1002 73     | 1/10 | 22,23              | 11 | 4010337113416 |
|  3-voudig                    | 0213 73     | 1/5  | 34,22              | 11 | 4010337113256 |
|  4-voudig                    | 0214 73     | 1/5  | 55,43              | 11 | 4010337113317 |
|  5-voudig                    | 0215 73     | 1/5  | 84,41              | 11 | 4010337113362 |

### Merkmale

- In de kleurvariant puur wit glanzend: bestaat voor 85 % uit bio-circulair kunststof.

### Technische Daten

|                     |                           |
|---------------------|---------------------------|
| Afdekraam 1-v:      | B 90,0 x H 90,0 x T 11,4  |
| Afdekkraam 2-v:     | B 90,0 x H 161,1 x T 11,4 |
| Afdekraam 2-v z/ms: | B 90,0 x H 161,1 x T 11,4 |

|                                      |                           |
|--------------------------------------|---------------------------|
| Afdekraam 3-v:                       | B 90,0 x H 232,6 x T 11,4 |
| Afdekraam 4-v:                       | B 90,0 x H 303,9 x T 11,4 |
| Afdekraam 5f:                        | B 90,0 x H 375,2 x T 11,4 |
| Hoekradius:                          | R 0,3                     |
| Biocirculair kunststof               |                           |
| - Kleurvariant: zuiver wit glanzend: | min. 50%                  |

---