







## Afdekraam Gira F300 antraciet (gelakt)



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 1-voudig	0211 83	1/10	12,60	11	4010337113461
 2-voudig	0212 83	1/10	19,13	11	4010337113515
 2-voudig zonder middenstijl	1002 83	1/10	19,13	11	4010337131878
 3-voudig	0213 83	1/5	31,46	11	4010337113560
 4-voudig	0214 83	1/5	51,10	11	4010337113614
 5-voudig	0215 83	1/5	77,75	11	4010337131861

### Merkmale

- In de kleurvariant puur wit glanzend: bestaat voor 85 % uit bio-circulair kunststof.

### Technische Daten

Afdekraam 1-v:	B 80,8 x H 80,8 x T 11,4
Afdekkraam 2-v:	B 80,8 x H 151,9 x T 11,4
Afdekraam 2-v z/ms:	B 80,8 x H 151,9 x T 11,4

Afdekraam 3-v:	B 80,8 x H 223,4 x T 11,4
Afdekraam 4-v:	B 80,8 x H 297,7 x T 11,4
Afdekraam 5f:	B 80,8 x H 366,0 x T 11,4
Hoekradius:	R 0,5
Biocirculair kunststof	
- Kleurvariant: zuiver wit glanzend:	min. 50%

---