










## Luidspreker inbouwradio IP System 55



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 crème wit glanzend	2282 01	1	28,44	03	4010337076230
 zuiver wit glanzend	2282 03	1	28,44	03	4010337076247
 zuiver wit mat	2282 27	1	28,44	03	4010337076254
 antraciet	2282 28	1	30,62	03	4010337076261
 kleur aluminium	2282 26	1	33,36	03	4010337076162
 zwart mat	2282 005	1	33,36	03	4010337037286
 grijs mat	2282 015	1	33,36	03	4010337083931
 edelstaal	2282 600	1	38,28	03	4010337032861

## Merkmale

- Luidspreker voor aansluiting op de Gira inbouwradio.

---

## Technische Daten

Inbouwdiepte:	32 mm
Aansluitingdoorsnede - Luidspreker-/AUX-aansluiting:	1.5mm <sup>2</sup>
Impedantie:	8 Ω
Omgevingstemperatuur:	-5 °C tot +50 °C

---