

## Luidspreker inbouwradio IP



| Specificatie                                                                                                 | Art. nr. | VE | EUR/stuk excl. BTW | PS | EAN           |
|--------------------------------------------------------------------------------------------------------------|----------|----|--------------------|----|---------------|
|  crème wit glanzend         | 2282 01  | 1  | 28,44              | 03 | 4010337076230 |
|  zuiver wit glanzend      | 2282 03  | 1  | 28,44              | 03 | 4010337076247 |
|  zuiver wit mat           | 2282 27  | 1  | 28,44              | 03 | 4010337076254 |
|  antraciet                | 2282 28  | 1  | 30,62              | 03 | 4010337076261 |
|  kleur aluminium (gelakt) | 2282 26  | 1  | 33,36              | 03 | 4010337076162 |
|  zwart mat (gelakt)       | 2282 005 | 1  | 33,36              | 03 | 4010337037286 |
|  grijs mat (gelakt)       | 2282 015 | 1  | 33,36              | 03 | 4010337083931 |
|  edelstaal                | 2282 600 | 1  | 38,28              | 03 | 4010337032861 |
|  in zwartglaslook         | 2282 05  | 1  | 38,28              | 03 | 4010337889182 |

## Kenmerken

- Luidspreker voor aansluiting op de Gira inbouwradio.

---

## Technische gegevens

|                                                         |                    |
|---------------------------------------------------------|--------------------|
| Inbouwdiepte:                                           | 32 mm              |
| Aansluitingdoorsnede<br>- Luidspreker-/AUX-aansluiting: | 1.5mm <sup>2</sup> |
| Impedantie:                                             | 8 $\Omega$         |
| Omgevingstemperatuur:                                   | -5 °C tot +50 °C   |

---