


## Voeding DC 24 V 700 mA



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 DIN-rail	2570 00	1	113,19	18	4010337025702

### Technische Daten

Nominale spanning - primair:	AC 230 V, 50 Hz
Nominale spanning secundair - secundair:	DC 24 V SELV
Nominale stroom secundair:	0,7 A
Zekering:	elektronisch, met automatische resetfunctie
Omgevingstemperatuur:	-5 °C tot +40 °C

### Abmessungen

Teilungseinheiten (TE):	6
-------------------------	---