








Aardlekschakelaar 30 mA



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWhSt.	PS	EAN
 crème wit glanzend	2664 01	1	167,90	03	4010337011897
 zuiver wit glanzend	2664 03	1	167,90	03	4010337011903
 zuiver wit mat	2664 27	1	167,90	03	4010337011910
 antraciet	2664 28	1	168,58	03	4010337011927
 kleur aluminium	2664 26	1	170,28	03	4010337011934
 zwart mat	2664 005	1	170,28	03	4010337037064
 grijs mat	2664 015	1	170,28	03	4010337085232

Merkmale

- De aardlekschakelaar is een vaste beveiligingsinrichting met spanningsonafhankelijke lekstroomactivering conform VDE 0664.
- Werkingsprincipe komt overeen met dat van een aardlekschakelaar.

Technische Daten

Nominale spanning:	AC 230 V, 50/60 Hz
Nominale stroom:	16 A
Nominale lekstroom:	30 mA
Inbouwdiepte:	32 mm
Aansluitingdoorsnede - voor geleiders van:	1,5 mm ² tot 2,5 mm ²
Omgevingstemperatuur:	-25 °C tot +40 °C

Hinweise

- Toepassingsgebieden: Wandgoten, voor wandcontactdozen of in Gira energiezuilen.
 - Montage in een diepe apparaatdoos.
-