

## Universele uit-wisselschakelaar



| Specificatie                                                                                                 | Art. nr. | VE   | EUR/stuk excl. BTW | PS | EAN           |
|--------------------------------------------------------------------------------------------------------------|----------|------|--------------------|----|---------------|
|  crème wit glanzend         | 2832 01  | -    | -                  | -  | 4010337832010 |
|  zuiver wit glanzend      | 2832 03  | 1/10 | 36,52              | 29 | 4010337832034 |
|  antraciet                | 2832 28  | 1/10 | 39,25              | 29 | 4010337832287 |
|  kleur aluminium (gelakt) | 2832 26  | 1/10 | 43,42              | 29 | 4010337832263 |
|  zwart mat (gelakt)       | 2832 005 | 1/10 | 43,42              | 11 | 4010337038528 |
|  grijs mat (gelakt)       | 2832 015 | 1/10 | 43,42              | 11 | 4010337087120 |

### Technische gegevens

Inbouwdiepte: 25 mm

Aansluitingdoorsnede  
- voor geleiders tot: 2,5 mm<sup>2</sup>

## Aanwijzingen

- Uitsluitend voor schroefbevestiging.

---