








Wipdrukcontact 3-voudig 10 A 250 V~met wippen Maakcontact 1-polig



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 crème wit glanzend	2844 01	1/10	38,42	29	4010337082033
 zuiver wit glanzend	2844 03	1/10	38,42	29	4010337082040
 antraciet	2844 28	1/10	41,20	29	4010337082064
 kleur aluminium	2844 26	1/10	45,30	29	4010337082057
 zwart mat	2844 005	1/10	45,30	29	4010337037903
 grijs mat	2844 015	1/10	45,30	29	4010337087182
 edelstaal (gelakt)	2844 600	1/10	49,19	29	4010337021957

Technische Daten

Inbouwdiepte:	25 mm
Aansluitingdoorsnede - voor geleiders tot:	2,5 mm ²

Hinweise

- Uitsluitend voor schroefbevestiging.
