

Wipschakelaar 10 AX 250 V~ met wip 2-voudig voor weergave hotelkamerstatus



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 crème wit glanzend	3104 01	1	41,21	01	4010337042495
 zuiver wit glanzend	3104 03	1	41,21	01	4010337042501
 zuiver wit mat	3104 27	1	41,21	01	4010337042525
 antraciet	3104 28	1	41,73	11	4010337042532
 kleur aluminium	3104 26	1	45,13	11	4010337042518
 zwart mat	3104 005	1	45,13	11	4010337069812

Merkmale

- Schakelaar voor weergave hotelkamerstatus "Do not disturb" en "Make up room".
- Met vergrendeling tegen dubbelzijdig inschakelen.
- Elektrisch en mechanisch vergrendeld.

Technische Daten

Inbouwdiepte:	32 mm
Aansluitingdoorsnede	
- voor massieve en soepele geleiders tot:	2,5 mm ²

Nominaal vermogen
- LEDi/ CFLi:

100 W
