










Draagring Modular Jack 2-voudig Draagring MJ-01 tot MJ-10



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Draagring MJ-01	5601 00	1/10	7,55	01	4010337460015
 Draagring MJ-02	5602 00	1/10	7,55	01	4010337460022
 Draagring MJ-03	5603 00	1/10	7,55	01	4010337460039
 Draagring MJ-04	5604 00	1/10	7,55	01	4010337460046
 Draagring MJ-05	5605 00	1/10	7,55	01	4010337460053
 Draagring MJ-06	5606 00	1/10	7,55	01	4010337460060
 Draagring MJ-07	5607 00	1/10	7,55	01	4010337460077
 Draagring MJ-08	5608 00	1/10	7,55	01	4010337460084
 Draagring MJ-09	5609 00	1/10	7,55	01	4010337460091



Draagring MJ-10

5610 00

1/10

7,55

01

4010337460107

Technische Daten

Afmetingen

- MJ-01, MJ02, MJ-07:	B 14,8 x 19,5 mm
- MJ-03:	B 14,8 x H 20,0 mm
- MJ-04, MJ-09:	B 14,8 x 19,3 mm
- MJ-05:	B 16,7 x H 17,3 mm
- MJ-06:	B 15,9 x H 18,3 mm
- MJ-08:	B 14,8 x H 19,0 mm
- MJ-10:	B 16,1 x H 18,5 mm

Hinweise

- Uitsluitend voor schroefbevestiging.
 - Geschikt voor wandgootinstallatie.
-